

让工作更轻松!

轻松液压胀管器



简单操作五步骤



① 铜管去毛刺, 硬管需退火处理



② 将胀头旋到胀管器上



③ 将管子末端放到胀头上



④ 反复压手柄直到管子完全胀开



⑤ 胀管完成, 取下胀好的管子

轻松胀管

液压胀管

- 使用更轻松
- 适用于更大管径胀管

结构紧凑

- 适用于狭小空间
- 使用更简单

快速装卸

- 四头大螺距螺纹, 1秒锁紧胀头

单手操作

- 减轻劳动强度, 提高工作效率

自动泄压

- 胀管完成后胀头自动复位

型号	VHE-29D	VHE-42D
胀管管径	3/8", 1/2", 5/8", 3/4", 7/8", 1", 1-1/8"	3/8", 1/2", 5/8", 3/4", 7/8", 1", 1-1/8", 1-1/4", 1-3/8", 1-1/2", 1-5/8"
配件	VTT-5, VTC-32	VTT-5, VTC-42